



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FSC12 2G FSC BX *Crouse-Hinds*

Catalog Number	FSC12
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet FS Device Box, Shallow, Feraloy Iron Alloy, Two-Gang, C Shape, 1/2"
Weight per unit	3.5 (lbs/each)
Product Category	FS & FD Type Boxes & Covers

Features

Cable Entry	(1) Each Side
dimensions	4.1900 IN X 1.8800 IN X 6.0600 IN
Material	ElectroGalvanized With Aluminum Acrylic Painted Feraloy Iron Alloy

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Description	2G FSC BX
extra long description	CRS-H FSC12 1/2 NPT CST IRON FS BX
Features	Crouse-Hinds series FS and FD device boxes are installed in non-hazardous area conduit systems to accommodate wiring devices, act as pull boxes or provide openings for taps and splices. They are suitable for use in wet locations when used with gasketed covers. FS and FD device boxes are available in two box depths with a wide variety of gang configurations, hub configurations and hub sizes. They are manufactured in cast iron, aluminum, stainless steel and malleable iron. Malleable iron boxes are also a
Long Description	Eaton Crouse-Hinds series Condulet FS device box, Shallow, Feraloy iron alloy, Two-gang, C shape, 1/2"
Product Type	1/2 NPT CST Iron FS BX Two GNG MTG Lugs
Special Features	Configuration Type FSC, With Mounting Lug And Ground Screw, Dimension 4-5/8 In Width X 1-7/8 In Depth X 6-1/16 In Height

Manufacturer Information

Brand	Eaton
GTIN	00782274411200
Manufacturers Part Number	FSC12
UPC	782274411200



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description FS BOXES AND COVERS

Type DEVICE BOX

Packaging

Carton 1

Package 2

Weight Per each 3.48

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Industrial Facilities/Factories - Other

Mounting SURFACE

standard UL 514, ANSI C33.84, CSA C22.2, Federal Specification W-C-5860