

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



FWX35A 250V Semiconduct Fuse

Bussmann Fuses

Taxonomies, Classifications, and Categories
Category Description Fuse:

Type

Catalog Number	E/V/X2EV
Catalog Number Manufacturer	FWX35A Bussmann Fuses
Description	Eaton Bussmann Series FWX High Speed Fuse, 600V, 35A RMS,
Description	200 Kaic Vac, 50 Kaic At 250 VDC, Non Indicating, High Speed Fuse, Blade End X Blade End, Stud
Weight per unit	0.1500 (lbs/each)
Product Category	Semiconductor, Rectifier, & Hi
eatures	
amperage rating	35
connection	Blade End X Blade End
dimensions	3.4400 IN X 0.9100 IN X 0.8900 IN
interrupt rating	50 kAIC at 250 Vdc200 kAIC Vac
Voltage Rating	600 V
escriptions	
Description	250V SEMICONDUCT FUSE
extra long description	EFSE FWX-35A BUSS HIGH SPEED FUSE
Features	High speed fuses provide superior protection or isolation for components such as diodes, silicon controlled rectifiers (SCRs), Gate torn-Off Thyristors (GTOs) and IGBTs and in light and heave harsh DC traction applications as high as 4000Vdc and 10,000A Also used for the protection of DC link/power converters. Optimized dimensions and materials allow for excellent thermal dissipation for high current cycling environments, or heavy dutapplications.
Long Description	Eaton Bussmann series FWX high speed fuse, 600V, 35A RMS, 200 kAIC Vac, 50 kAIC at 250 Vdc, Non Indicating, High speed fuse, Blade end X blade end, Stud
Product Type	Buss High Speed Fuse
anufacturer Information	
Brand	Eaton
GTIN	00051712150477
Manufacturers Part Number	FWX35A
UPC	051712150477

Fuses & Fuse Accessories

High speed fuse



ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Packaging	
Carton	5
Weight Per each	0.15
Uses, Certifications, and Standards	
Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	UL Recognized,CSA Certified,RoHS Compliant,CE Marked