



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FXS1510 10' Fiberglass Step/Shelf Ladder Ia *Louisville Ladder*

Catalog Number	FXS1510
Manufacturer	Louisville Ladder
Description	Step Ladder, Double Entry, Cross Step Type; Fiberglass Material; 29.29 Inch Base Width; 10 Foot Height to Top Step; 3 Inch Rung Width; 39 Pound Weight; 300 Pound Load Rating; 10 Step(S); Duty Rating Type Ia; Applicable Standard Csa, Asha, Ansi
Weight per unit	37.5 (lbs/each)
Product Category	Hand Tools - Ladders

### Features

Base Width	29.29 Inch
Height to Top Step	10 Foot
Load Rating	300 Pound
Material	Fiberglass
number of steps	10
Rung Width	3 INCH

### Descriptions

Additional Information	Duty Rating Type IA; Applicable Standard CSA, ASHA, ANSI
Commodity Description	LADDERS
Description	10' FIBERGLASS STEP/SHELF LADDER IA
extra long description	CROSS STEP, 2-IN-1 TYPE; FIBERGLASS MATERIAL; 29-1/4 INCH BASE WIDTH; 39 POUND WEIGHT; 300 POUND LOAD RATING; 10 STEP(S); 48 INCH BASE SPREAD; RUNG SIZE 3 INCH DEPTH; RUNG TYPE STANDARD STEP; DUTY RATING TYPE IA; LADDER SIZE 10 FOOT; MAXIMUM REACH 13 FOOT 3 INCH FOOT (SHELF LADDER), 14 FOOT 2 INCH (STEP LADDER); MAXIMUM STANDING HEIGHT 6 FOOT 8 INCH (SHELF LADDER), 7 FOOT 7 INCH (STEP LADDER); APPLICATION ROOFING, BUILDING MAINTENANCE, CONTRACTING AND INDUSTRIAL CONSTRUCTION; APPLICABLE STANDARD ANSI A14.5
Long Description	STEP LADDER, DOUBLE ENTRY, CROSS STEP TYPE; FIBERGLASS MATERIAL; 29.29 INCH BASE WIDTH; 10 FOOT HEIGHT TO TOP STEP; 3 INCH RUNG WIDTH; 39 POUND WEIGHT; 300 POUND LOAD RATING; 10 STEP(S); DUTY RATING TYPE IA; APPLICABLE STANDARD CSA, ASHA, ANSI
Product Type	Step Ladder



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Louisville Ladder
GTIN	00728865133168
Manufacturers Part Number	FXS1510
Model	FXS1500
UPC	728865133168

## Taxonomies, Classifications, and Categories

Category Description	LADDERS
Type	Double Entry, Cross Step

## Packaging

Carton	1
Weight	39 Pound
Weight Per each	37.5006