



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



GBC210 10CKT Isol Ground Bar

Nsi Industries

Catalog Number	GBC210
Manufacturer	Nsi Industries
Description	The Nsi GBC2-10 Copper Isolated Ground Bar Mounts Onto Most Surfaces Using The High-Strength Glass-Filler Polyester Base, Then Fits Up to 10 Copper Cables In The 2 to 14 Awg Size Range. The High-Conductivity Copper Body Is Rated For Use With Copper Wiring and Forms Reliable Connections Using The Simple Tightening Screw Lug Design. Stock Products You Can Rely Onâ€”Stock Nsi.
Weight per unit	1.4 (lbs/each)
Product Category	Ground Rods & Grounding System

Features

Conductor Size	2-14 AWG
insulation	Glass Filled Polyester Base
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

Dimensions and Weight

Length	4.07
Size	2-14 AWG



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Descriptions

Description	10CKT ISOL GROUND BAR
extra long description	NSI GBC2-10 Copper Isolated Ground
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These copper isolated grounding bars offer a convenient and reliable solution for grounding multiple copper cables. The high-conductivity copper bar and high-strength glass-filled polyester base are both designed for long-lasting performance in a variety of environments. Designed to fit a range of different wire sizes by using a screw lug design, these
Long Description	The NSI GBC2-10 Copper Isolated Ground Bar mounts onto most surfaces using the high-strength glass-filler polyester base, then fits up to 10 copper cables in the 2 to 14 AWG size range. The high-conductivity copper body is rated for use with copper wiring and forms reliable connections using the simple tightening screw lug design. Stock products you can rely on are stock NSI.
Product Type	Copper Isolated Ground Bar, 2-14 Awg Wire Range, 10 Circuit
Special Features	Copper Bar With Isolation Base - 10 Circuits

Manufacturer Information

Brand	Polaris
GTIN	00662381010735
Manufacturers Part Number	GBC2-10
UPC	662381010735

Taxonomies, Classifications, and Categories

Category Description	EXOTHERMIC GROUNDING PRODUCTS
Type	Isolated Ground Bars

Packaging

Carton	1
Package	3
Weight Per each	1.4

Uses, Certifications, and Standards

Application	Grounding Wire
-------------	----------------