



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GC75 3/4" Flex Conn D/C Screw In *Appleton/Oz Gedney*

| | |
|------------------|--|
| Catalog Number | GC75 |
| Manufacturer | Appleton/Oz Gedney |
| Description | Features:0.83IN Dia X 1.63IN Length, For Flexible Metal Conduit, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.75IN, Material:Zinc Die Cast |
| Weight per unit | 0.0900 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|-----------------|
| angle | Straight |
| connection | Male NPS Thread |
| Connector Type | Screw In |
| insulation | Non Insulated |
| Material | Zinc Die Cast |

Material, Color, and Finish

| | |
|--------|----------|
| Color | Metallic |
| Finish | Natural |

Dimensions and Weight

| | |
|------|------|
| Size | 0.75 |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 3/4" FLEX CONN D/C SCREW IN |
| extra long description | EGS GC-75 3/4 IN SCREW IN CONN |
| Long Description | Features:0.83IN Dia X 1.63IN Length, For Flexible Metal Conduit, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.75IN, Material:Zinc Die Cast |
| Product Type | 3/4 In Screw In Conn |
| Special Features | 0.83 IN Dia X 1.63 IN Length, For Flexible Metal Conduit |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Appleton |
| GTIN | 00687855203758 |
| Manufacturers Part Number | GC75 |
| UPC | 687855203758 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | Screw In Connector |

Trade Size

| | |
|------------|------|
| Trade Size | 0.75 |
|------------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.09 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Screw-In Connector for flexible metal conduit |
| environmental conditions | Dry Location |
| nema rating | FB-1 |
| standard | UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No. 18.3, CSA Certified: 208044; NEMA: FB-1 |