



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GCA4 2-1/2" - 4" Alum Ground Clamp

*Nsi Industries*

Catalog Number	GCA4
Manufacturer	Nsi Industries
Description	The Nsi Gca-4 Aluminum Ground Clamp For 250 MCM to 6 Awg Aluminum and Copper Cables Grips On Water Pipes, Galvanized Pipe or Steel Conduit Between 2-1/2" to 4" Ips Pipes. The High-Strength Extruded Aluminum Alloy Design Is Plated to Provide Low-Contact Resistance and Features Zinc-Plated Steel Set Screws For Long-Term Installation. Use This Adjustable Clamp to Ground Copper or Aluminum Cables to Pipes and Conduit In Indoor Environments. Ul Listed 467 For Grounding and Bonding. Stock Products You Can Rely O
Weight per unit	1.0 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Clamp Material	250 MCM-6 AWG
Insulation Material	Aluminum



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	2-1/2" - 4" ALUM GROUND CLAMP
extra long description	NSI GCA-4 Ground Clamp Alum 2 1/2-4
Features	NSI grounding and bonding products rise to the occasion in a wide variety of environments with excellent material quality and flexible designs. These aluminum ground clamps offer a convenient and reliable solution for connecting copper or aluminum cables to pipes or conduit, using an adjustable clamping structure and a simple set screw tightening mechanism. Grips onto pipes tightly by using the zinc-plated steel screws to tighten the clamp, then fit your aluminum or copper cable into the grounding hole. NS
Long Description	The NSI GCA-4 Aluminum Ground Clamp for 250 MCM to 6 AWG Aluminum and Copper Cables grips on water pipes, galvanized pipe or steel conduit between 2-1/2" to 4" IPS pipes. The high-strength extruded aluminum alloy design is plated to provide low-contact resistance and features zinc-plated steel set screws for long-term installation. Use this adjustable clamp to ground copper or aluminum cables to pipes and conduit in indoor environments. UL Listed 467 for Grounding and Bonding. Stock products you can rely o
Product Type	Ground Clamp Alum 2 1/2-4"
Special Features	2 1/2-4 Pipe Size - Dual Rated Ground Clamp - Zinc Plated Screws

## Manufacturer Information

Brand	NSi
GTIN	00662381010025
Manufacturers Part Number	GCA-4
UPC	662381010025

## Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Aluminum Ground Clamp

## Packaging

Carton	3
Weight Per each	1.01

## Uses, Certifications, and Standards

Application	Grounding Wire
standard	cULus