



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GDB250MA 250V Fa Low-Break IEC Glass Fuse

*Bussmann Fuses*

Catalog Number	GDB250MA
Manufacturer	Bussmann Fuses
Description	Eaton GDB Series Fast-Acting Fuse, 0.250A, 250 Vac or Less, 32 VDC (Self Certified)
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

### Features

amperage rating	0.250A
connection	Ferrule End X Ferrule End
dimensions	X X 0.7874 IN
interrupt rating	35 AIC at 250 Vac
Material	Glass tube Nickel-plated brass end cap construction
Voltage Rating	250 Vac or less, 32 Vdc (self certified)

### Dimensions and Weight

Size	5.20 mm Diameter X 20.00 mm Height
------	------------------------------------

### Descriptions

Description	250V FA LOW-BREAK IEC GLASS FUSE
extra long description	EFSE GDB-250MA BUSS SMALL DIMENSION
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse
Long Description	Eaton GDB Series Fast-acting fuse, 0.250A, 250 Vac or less, 32 Vdc (self certified)
Product Type	Buss Small Dimension Fuse
Special Features	Low Breaking Capacity, Interrupt Rating 35 Amp at 250 V, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Eaton
GTIN	00051712431705
Manufacturers Part Number	GDB-250MA
UPC	051712431705



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse

## Packaging

Carton	5
Weight Per each	0.01

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
Frequency Rating	50
standard	VDE,CE Marked,CCC Marked,RoHS Compliant