



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GLA250 250 MCM Lay In Connector

Nsi Industries

Catalog Number	GLA250
Manufacturer	Nsi Industries
Description	Lay In Connector 250 MCM - 6 Awg Lay-In Connectors Offer The Ultimate In Flexibility. Excellent For Grounding and Continuous Loop Applications. Made Of 6061T-6 Aluminum Alloy. Electro-Tin Plated For Low Contact Resistance. Suitable For Use With Both Copper and Aluminum Conductors. Rated 600V (2000V Max. Per UL486B). UI 486A/B Listed. Temperature Rating 90 Degrees C.
Weight per unit	0.1800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	1
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Al/Cu

Material, Color, and Finish

Color	Aluminum
Finish	Aluminum

Dimensions and Weight

Size	L=2.20 - H=1.70 - W=.800
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	250 MCM LAY IN CONNECTOR
extra long description	NSI GLA-250 AL 250 MCM Lay In Conne
Features	Lay In Connector 250 MCM - 6 AWG Lay-in connectors offer the ultimate in flexibility. Excellent for grounding and continuous loop applications. Made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600V (2000V max. per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C.
Long Description	Lay In Connector 250 MCM - 6 AWG Lay-in connectors offer the ultimate in flexibility. Excellent for grounding and continuous loop applications. Made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600V (2000V max. per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C.
Product Type	Al 250 MCM Lay In Connector
Special Features	250 MCM-6 AWG - Dual Rated - 20 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381001931
Manufacturers Part Number	GLA-250
UPC	662381001931

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Aluminum Lay-In Lug

Packaging

Carton	20
Weight Per each	0.18

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	cULus
Temperature Rating	90 C