



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLC12HDB Ground Clamp

*Nsi Industries*

Catalog Number	GLC12HDB
Manufacturer	Nsi Industries
Description	Nsi GLC-12HDB Heavy Duty Direct Burial Ground Clamps Grip On Pipes Between 1/2" to 1" In Diameter and Are The Ultimate Ground Clamps For Securing Just About Any Size Ground Wire In Just About Any Application. The Bronze Body and Pre-Assembled 304 Stainless Steel Screws Are Made Of Economical, High-Quality Metals That Provide Durable Performance In A Range Of Applications. The Horizontal Lay-In Lug Design Of These Clamps Provides Ultimate Flexibility When Securing Large Conductors and Can Accommodate Wires
Weight per unit	0.3100 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Material	Cast Bronze
Warranty	1 YEAR

### Material, Color, and Finish

Clamp Material	Cast Bronze
Color	Bronze
Insulation Color	Bronze
Insulation Material	Silicon Bronze

### Dimensions and Weight

Length	2.362
--------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	GROUND CLAMP
extra long description	NSI GLC-12HDB Gnd Clamp Lay-In 1/2-
Features	NSI grounding and bonding products rise to the occasion in a wide variety of indoor and outdoor environments with excellent material quality and flexible designs. These heavy-duty bronze ground clamps with lay-in lugs offer the ultimate solution for grounding large wires in just about any application. Grips onto copper water pipes, tubing, rebar and ground rods using 304 stainless steel screws to tighten the clamp, then grounding conductor is secured in place using a lay-in lug design for ultimate flexibil
Long Description	NSI GLC-12HDB Heavy Duty Direct Burial Ground Clamps grip on pipes between 1/2" to 1" in diameter and are the ultimate ground clamps for securing just about any size ground wire in just about any application. The bronze body and pre-assembled 304 stainless steel screws are made of economical, high-quality metals that provide durable performance in a range of applications. The horizontal lay-in lug design of these clamps provides ultimate flexibility when securing large conductors and can accommodate wires
Product Type	GND Clamp Lay-In 1/2-1" - Horizontal
Special Features	UL 486D Listed

## Manufacturer Information

Brand	NSi
GTIN	00662381005366
Manufacturers Part Number	GLC-12HDB
UPC	662381005366

## Taxonomies, Classifications, and Categories

Category Description	EXOTHERMIC GROUNDING PRODUCTS
Type	Heavy Duty Direct Burial Lay-In Lug

## Packaging

Carton	1
Weight Per each	0.31

## Uses, Certifications, and Standards

Application	Grounding Wire
standard	cULus