



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GL25048 250MCM 1-Hole Compression Lug 1/2" Bolt

*Nsi Industries*

Catalog Number	GL25048
Manufacturer	Nsi Industries
Description	1 Hole Short Barrel Copper Compression Lug W/ Peep Hole 250 MCM - 1/2" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.1300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	250 MCM (STR)
Material	Copper
Number of Holes	1
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Yellow
Finish	Tin Plated

### Dimensions and Weight

Size	L=2.48 - W=1.09 - OD=.750 - ID=.590
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	250MCM 1-HOLE COMPRESSION LUG 1/2" BOLT
extra long description	NSI GL25048 CU CMP Lug Short 250 MC
Features	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 250 MCM - 1/2" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 250 MCM - 1/2" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Lug Short 250 MCM 1/2 Bolt Size
Special Features	250 MCM (STR) - 1/2 Mounting Hole

## Manufacturer Information

Brand	NSi
GTIN	00662381036148
Manufacturers Part Number	GL25048
UPC	662381036148

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole

## Packaging

Carton	1
Package	25
Weight Per each	0.13

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Hole
standard	UL486A/B