



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

15152 E Fremont Dr
80112-0000, CO Centennial
Phone: 720-278-7555
Fax: 720-259-8851



GRP30175 30" 175LB HD Natural CBL Tie

Nsi Industries

Catalog Number	GRP30175
Manufacturer	Nsi Industries
Description	The Powergrp GRP-30175 50-Count Resealable Pack Of Type 21 Natural-Colored Super Heavy-Duty Cable Ties Are 30" Long, With 175LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 30" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .28" (7MM) and 8.98" (228MM) Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and S
Weight per unit	1.6 (lbs/each)
Product Category	Tools & Testers

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Finish	Natural
--------	---------

Descriptions

Description	30" 175LB HD NATURAL CBL TIE
-------------	------------------------------

extra long description	NSI GRP-30175 Cable Tie 30 IN 175Lb
------------------------	-------------------------------------

Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-30175 ties combine a self-locking design with an industrial strength 175lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-30175 ties are water
----------	---

Long Description	The PowerGRP GRP-30175 50-Count Resealable Pack of Type 21 Natural-Colored Super Heavy-Duty Cable Ties are 30" long, with 175lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 30" cables ties around a wide range of equipment with a bundle diameter between .28" (7mm) and 8.98" (228mm) using the bent tips and serrated locking mechanism to form an effortless and s
------------------	---

Product Type	Cable Tie 30 In 175LB Nat (50PK)
--------------	----------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

15152 E Fremont Dr
80112-0000, CO Centennial
Phone: 720-278-7555
Fax: 720-259-8851

Manufacturer Information

Brand	Powergrp
GTIN	00662381009456
Manufacturers Part Number	GRP-30175
UPC	662381009456

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

Availability

minimum qty	50
-------------	----

Packaging

Carton	1
Package	50
Weight Per each	1.55

Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F