

## Specification Sheet

Part Number: GT.75X1800



Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

**Article Number**

854-44384

**Type**

GT.75X180

**Color**

Black (BK)

**Features & Benefits**

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

**Quantity Per**

bag

**Product Description**

For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

**Short Description**

Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

**Global Part Name**

GT.75X180

**Length L (Imperial)**

15.0

**Length L (Metric)**

4.5

**Width W (Imperial)**

0.75

**Width W (Metric)**

19.05

**Material**

Polyethylene (PE) Polyamide 6 (PA6)

**Material Shortcut**

PE PA66

**UL Recognized (US)**

Yes

**UL Recognized (US and Canada)**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

9606100000



## Specification Sheet

Part Number: GT.75X1800



Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

**Article Number**

854-44384

**Type**

GT.75X180

**Color**

Black (BK)

**Features & Benefits**

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

**Quantity Per**

bag

**Product Description**

For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

**Short Description**

Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

**Global Part Name**

GT.75X180

**Length L (Imperial)**

15.0

**Length L (Metric)**

4.5

**Width W (Imperial)**

0.75

**Width W (Metric)**

19.05

**Material**

Polyethylene (PE) Polyamide 6 (PA6)

**Material Shortcut**

PE PA66

**UL Recognized (US)**

Yes

**UL Recognized (US and Canada)**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

9606100000

