



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## GRP850 8" 50LB WHT CBL Tie

*Nsi Industries*

Catalog Number	GRP850
Manufacturer	Nsi Industries
Description	The Powergrp GRP-850 100-Count Resealable Pack Of Type 21S Ah-2 Natural-Colored General-Purpose Cable Ties Are 8" Long, With 50LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 8" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .12" (3MM) and 2.09" (53MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and
Weight per unit	0.3450 (lbs/each)
Product Category	Tools & Testers

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Finish	Natural
--------	---------

### Descriptions

Description	8" 50LB WHT CBL TIE
extra long description	NSI GRP-850 PowerGRP Cable Tie Natu
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-850 ties combine a self-locking design with a general purpose 50lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-850 ties are waterproof and
Long Description	The PowerGRP GRP-850 100-Count Resealable Pack of Type 21S AH-2 Natural-Colored General-Purpose Cable Ties are 8" long, with 50lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 8" cables ties around a wide range of equipment with a bundle diameter between .12" (3mm) and 2.09" (53mm), using the bent tips and serrated locking mechanism to form an effortless and
Product Type	Powergrp Cable Tie Natural 8" 50LB (100PK)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381009135
Manufacturers Part Number	GRP-850
UPC	662381009135

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	1
Package	100
Weight Per each	0.345

## Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F