



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GUAL59SA 1-1/2" Alu Body&CVR

Crouse-Hinds

Catalog Number	GUAL59SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Gua Conduit Outlet Box With Cover, 5" Cover Opening Diameter, Copper-Free Aluminum, L Shape, 1-1/2"
Weight per unit	4.4 (lbs/each)
Product Category	Alum

Features

Cable Entry dimensions	(2) Side 6.8100 IN X 4.0300 IN X 6.8100 IN
------------------------	---

Dimensions and Weight

Size	1-1/2 in
------	----------

Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	1-1/2" ALU BODY&CVR
extra long description	CRS-H GUAL59 SA 1 1/2 AL ROUND BASE
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th
Long Description	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 5" cover opening diameter, Copper-free aluminum, L shape, 1-1/2"
Product Type	1 1/2 Al Round Base Outlet 5 In CVR
Special Features	With Cover, Cover Opening Diameter 5 In

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274100418
Manufacturers Part Number	GUAL59 SA
UPC	782274100418

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.4499

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2