



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUAT24 3/4" Guat Cond Body&CVR

*Crouse-Hinds*

Catalog Number	GUAT24
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Gua Conduit Outlet Box With Cover, 2" Cover Opening Diameter, Feraloy Iron Alloy, T Shape, 3/4"
Weight per unit	1.8 (lbs/each)
Product Category	Bodies & Covers

### Features

Cable Entry	(3) Side
dimensions	4.2500 IN X 2.0000 IN X 3.3800 IN

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	3/4" GUAT COND BODY&CVR
extra long description	CRS-H GUAT24 3/4 OUTLET BX 2 CVR FO
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th
Long Description	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 2" cover opening diameter, Feraloy iron alloy, T shape, 3/4"
Product Type	3/4 Outlet BX 2 CVR For THRD Rigid/Imc
Special Features	With Cover, Cover Opening Diameter 2 In

### Manufacturer Information

Brand	Eaton
GTIN	00782274467405
Manufacturers Part Number	GUAT24
UPC	782274467405

### Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	2
Weight Per each	1.83

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2