



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GUAN24 3/4" Outlet Box 2 Dia CVR For THRD Rigid *Crouse-Hinds*

Catalog Number	GUAN24
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Gua Conduit Outlet Box With Cover, 2" Cover Opening Diameter, Feraloy Iron Alloy, N Shape, 3/4"
Weight per unit	N/A
Product Category	Bodies & Covers

Features

Cable Entry dimensions	(2) Side 3.3800 IN X 2.3100 IN X 3.3800 IN
------------------------	---

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	3/4" OUTLET BOX 2 DIA CVR FOR THRD RIGID
extra long description	CRS-H GUAN24 3/4 OUTL BX 2 DIA CVR
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th
Long Description	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 2" cover opening diameter, Feraloy iron alloy, N shape, 3/4"
Product Type	3/4 Outl BX 2 Dia CVR THRD Rigid/Imc
Special Features	With Cover, Cover Opening Diameter 2 In

Manufacturer Information

Brand	Eaton
GTIN	00782274466408
Manufacturers Part Number	GUAN24
UPC	782274466408

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting	PAD
standard	UL 886, CSA C22.2