



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUV7825 U Bolt Ground Clamp

*Abb Installation Products, Inc*

Catalog Number	GUV7825
Manufacturer	Abb Installation Products, Inc
Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250 Kcmil, Rod Size 7/8 - 1 Inch, Ips Pipe Size 1/2 - 3/4 Inch, Length 2-3/4 Inches, Width 2-5/8 Inches, Depth 1-9/16 Inches
Weight per unit	0.6450 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Conductor Size	2/0 AWG - 250kcmil
insulation	No

### Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

### Dimensions and Weight

Length	2-3/4 in
--------	----------

### Descriptions

Description	U BOLT GROUND CLAMP
extra long description	ABB GUV7825 U BOLT GRD CLAMP CONDUCT
Long Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250 kcmil, Rod Size 7/8 - 1 Inch, IPS Pipe Size 1/2 - 3/4 Inch, Length 2-3/4 Inches, Width 2-5/8 Inches, Depth 1-9/16 Inches
Product Type	U Bolt GRD Clamp Conductor 250-2/0
Special Features	Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area

### Manufacturer Information

Brand	Blackburn Grounding
GTIN	00783786803552
Manufacturers Part Number	GUV7825
UPC	783786803552

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GROUND CLAMP

### Packaging

Carton	25
Weight Per each	0.645



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

standard

UL E3060, CSA 12798

---