



Work gloves are available in a wide variety of fabrics and styles; Cotton, Canvas, Jersey (lined and Unlined), PVC Coated, Cowhide, Deerskin and Pigskin. Additionally Top Sellers include the Super Gripper, a latex dipped cool cotton glove which resists punctures, cuts and abrasions. Our Dottie exclusive line of Techwear™ a form fitting glove that is so comfortable it feels like it's a part of your hand. Techwear™ is available in three color coded styles.

CAT NO	UPC	SIZE	DESCRIPTION	STD	MSTR	WT/STD	UNIT
GV10	24120	Fits All	Med Weight White String Knit	1	12	0.190#	Pair
GV11	24121	Fits All	8oz Cotton Canvas, Blue Knit Wr.	1	12	0.190#	Pair
GV12	24122	Fits All	8oz Canvas w/ PVC Dots, Knit Wr.	1	12	0.240#	Pair
GV14	24123	Fits All	Heavy Weight Brown Jersey Knit Wr.	1	12	0.140#	Pair
GV16	24124	Fits All	Brown Jersey/Red Fleece Lining	1	12	0.200#	Pair
GV20M	24150	Medium	Cotton Knit Super Gripper	1	12	0.210#	Pair
GV20L	24151	Large	Cotton Knit Super Gripper	1	12	0.220#	Pair
GV20X	24152	Extra Large	Cotton Knit Super Gripper	1	12	0.240#	Pair
GV22M	24126	Medium	Leather Palm w/ Canvas Cuff	1	12	0.490#	Pair
GV22L	24127	Large	Leather Palm w/ Canvas Cuff	1	12	0.600#	Pair
GV22X	24128	Extra Large	Leather Palm w/ Canvas Cuff	1	12	0.600#	Pair
GV30M	24129	Medium	Rust Split Leather Drivers	1	12	0.380#	Pair
GV30L	24130	Large	Rust Split Leather Drivers	1	12	0.350#	Pair
GV30X	24131	Extra Large	Rust Split Leather Drivers	1	12	0.390#	Pair
GV35M	24132	Medium	Premium Pigskin Keystone	1	12	0.350#	Pair
GV35L	24133	Large	Premium Pigskin Keystone	1	12	0.350#	Pair
GV35X	24134	Extra Large	Premium Pigskin Keystone	1	12	0.350#	Pair
GV35ML	24148	Medium	Premium Pigskin Keystone Lined	1	12	0.370#	Pair
GV35LL	24146	Large	Premium Pigskin Keystone Lined	1	12	0.370#	Pair
GV35XL	24149	Extra Large	Premium Pigskin Keystone Lined	1	12	0.370#	Pair
GV42M	24135	Medium	Top Grain Leather Drivers Pull Strap	1	12	0.350#	Pair
GV42L	24136	Large	Top Grain Leather Drivers Pull Strap	1	12	0.350#	Pair
GV42X	24137	Extra Large	Top Grain Leather Drivers Pull Strap	1	12	0.400#	Pair
GV44M	24138	Medium	Top Grain Leather Drivers	1	12	0.340#	Pair
GV44L	24139	Large	Top Grain Leather Drivers	1	12	0.340#	Pair
GV44X	24140	Extra Large	Top Grain Leather Drivers	1	12	0.340#	Pair
GV52M	24141	Medium	Premium Deerskin Drivers	1	12	0.250#	Pair
GV52L	24142	Large	Premium Deerskin Drivers	1	12	0.280#	Pair
GV52X	24143	Extra Large	Premium Deerskin Drivers	1	12	0.290#	Pair



Latex Gloves and Shoe Covers
PC 6771



Latex Gloves

- Superior Quality
- Resistant To Most Residual Solvents And Chemicals
- Universal Fit
- Perfect For Finish Work

Shoe Covers

- Anti-Static
- Impervious Material
- Non-linting
- EZ On / EZ Off

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
LG100	59860	100 Latex Gloves in Jar	1	10	2.35#	Ea
SC	59880	50 Shoe Covers in Jar	1	10	0.90#	Ea