



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## H0759 90 Deg Male L/T Conn, 3/4", Steel *Hubbell Wiring Devices*

Catalog Number	H0759
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 3/4", Steel, Non-Insulated
Weight per unit	0.3500 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

connection	Cap Nut
Material	Steel, Zinc Plated
pallet quantity	3850

### Material, Color, and Finish

Color	Metallic
Finish	Metallic

### Dimensions and Weight

Size	3/4 in
Width	1.453

### Descriptions

Description	90 DEG MALE L/T CONN, 3/4", STEEL
extra long description	HWDK H0759 90 DEG MALE L/T CONN, 3/
Features	Insulated and Non-Insulated Conduit Connectors - Hubbell offers a broad line of metallic liquidtight fittings for use with metallic liq-uidtight conduits and Polytuff I. Hubbell offers trade sizes from 3/8" to 4" in straight, 45°, and 90° body designs. Most connectors are available with either insulated or non-insulated throats. Liquidtight fittings are precision manufactured to exacting standards assuring ease of use and reliability. Straight body 1/2" and 3/4" sizes are list-ed for UL Type 3R, 4, 12 and 13 envi
Long Description	Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 3/4", Steel, Non-Insulated
Product Type	Metallic Liquidtight Fittings
Special Features	Non-Insulated

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585034232
Manufacturers Part Number	H0759
UPC	783585034232



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Stainless Steel EMT Conduit
Type	Metallic Liquidtight Fittings

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	25
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit
environmental conditions	Suitable for use in wet locations when a listed sealing ring is used between box and fitting
Mounting	Between Enclosure and Conduit
nema rating	Suitable for use in hazardous locations per Class 1 Div 2
standard	CSA Certified;UL 514B