



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2433ST LKG Conn, 20A 3P 480V, L16-20R, B/W, SP *Hubbell Wiring Devices*

Catalog Number	HBL2433ST
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Edgeconnect™ Twist-Lock®, Industrial, Female Connector Body, 20A 3-Phase Delta 480V Ac, 3-Pole 4-Wire Grounding, L16-20R, Screwless Terminal, Black and White
Weight per unit	0.4500 (lbs/each)
Product Category	Wiring Devices

Features

connection	EdgeConnect™ Screwless Termination
Dielectric Strength	Withstands 3,000V minimum
Material	Nylon
Number of Wires	4
Phase	3
Poles	3
Voltage Rating	3P 480 VAC

Material, Color, and Finish

Color	Black and White
-------	-----------------

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	LKG CONN, 20A 3P 480V, L16-20R, B/W, SP
extra long description	HWDK HBL2433ST LKG CONN, 20A 3P 480
Features	EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result.
Long Description	Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Female Connector Body, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-20R, Screwless Terminal, Black and White
Product Type	LKG Conn, 20A 3P 480V, L16-20R, B/W, SP
Special Features	EdgeConnect™ Technology, Screwless Termination

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585719061
Manufacturers Part Number	HBL2433ST
series	EdgeConnect™
UPC	783585719061



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	CONNECTOR

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	30
Weight Per each	0.45

Uses, Certifications, and Standards

environmental conditions	IP20 Suitability
Mounting	Screw Mount
nema rating	L16-20R
standard	Listed to UL 498, Fed.Spec. W-C-596, Certified to CSA C22.2 No.42
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)