



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL2630 LKG RCPT, 30A 277V, 2P3W, L7-30R, BK *Hubbell Wiring Devices*

|                  |  |
|------------------|--|
| Catalog Number   | HBL2630  |
| Manufacturer     | Hubbell Wiring Devices   |
| Description      | Twist-Lock® Industrial Flush Receptacle, 30A 277V Ac, 2-Pole<br>3-Wire Grounding, L7, Screw Terminal |
| Weight per unit  | 0.2500 (lbs/each)  |
| Product Category | Gen Purpose Recept & Surge Pro   |

### Features

|                     |                           |
|---------------------|---------------------------|
| amperage rating     | 30                        |
| connection          | Screw Terminal            |
| Current Rating      | 30                        |
| Dielectric Strength | Withstands 2,000V minimum |
| Material            | Nylon                     |
| Number of Wires     | 3-Wire                    |
| pallet quantity     | 2520                      |
| Phase               | 1                         |
| Poles               | 2-Pole                    |
| Voltage Rating      | 277 VAC                   |
| Wattage             | 8,310                     |
| Wire Size           | #16 to #8                 |

### Dimensions and Weight

|      |                             |
|------|-----------------------------|
| Size | 3.28 in x 1.70 in x 1.31 in |
|------|-----------------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | LKG RCPT, 30A 277V, 2P3W, L7-30R, BK   |
| extra long description | HWDK HBL2630 LKG RCPT, 30A 277V, 2P  |
| Long Description       | Twist-Lock® Industrial Flush Receptacle, 30A 277V AC, 2-Pole<br>3-Wire Grounding, L7, Screw Terminal |
| Product Type           | LKG RCPT, 30A 277V, 2P3W, L7-30R, BK   |
| Special Features       | Standard   |

### Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585236056        |
| Manufacturers Part Number | HBL2630               |
| UPC                       | 783585236056          |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type                 | Single Flush Receptacle                             |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.25 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Heavy Duty Industrial   |
| environmental conditions | Indoor Dry unless protected by additional means                 |
| Mounting                 | Screw Mount   |
| nema rating              | L7-30R  |
| standard                 | Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498 |