



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5461W SGL RCPT, Ind GRD, 20A 250V, 6-20R, WH *Hubbell Wiring Devices*

Catalog Number	HBL5461W
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, White, Single Pack
Weight per unit	0.0820 (lbs/each)
Product Category	Wall Plates & Covers

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	5000
Wire Size	#12 to #10

Dimensions and Weight

Size	3.28 in x 1.63 in x 1.19 in
------	-----------------------------

Descriptions

Description	SGL RCPT, IND GRD, 20A 250V, 6-20R, WH
extra long description	HWDK HBL5461W SGL RCPT, IND GRD, 20
Long Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, White, Single Pack
Product Type	SGL RCPT, Ind GRD, 20A 250V, 6-20R, WH
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585001722
Manufacturers Part Number	HBL5461W
series	Extra Heavy Duty
UPC	783585001722

Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	SINGLE RECEPTACLE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.082

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	6-20R
standard	Certified to CSA 22.2, No. 42 File 285;Guide RTRT Fed Spec WC596G;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186