



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL5461W SGL RCPT, Ind GRD, 20A 250V, 6-20R, WH** *Hubbell Wiring Devices*

Catalog Number	HBL5461W
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, White, Single Pack
Weight per unit	0.1500 (lbs/each)
Product Category	Wall Plates & Covers

### **Features**

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	5,000
Wire Size	#12 to #10

### **Dimensions and Weight**

Size	3.28 in x 1.63 in x 1.19 in
------	-----------------------------

### **Descriptions**

Description	SGL RCPT, IND GRD, 20A 250V, 6-20R, WH
extra long description	HWDK HBL5461W SGL RCPT, IND GRD, 20
Long Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, White, Single Pack
Product Type	SGL RCPT, Ind GRD, 20A 250V, 6-20R, WH
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585001722
Manufacturers Part Number	HBL5461W
series	Extra Heavy Duty
UPC	783585001722

### **Taxonomies, Classifications, and Categories**

Category Description	Residential cord connectors
Type	SINGLE RECEPTACLE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	6-20R
standard	Certified to CSA 22.2, No. 42 File 285;Guide RTRT Fed Spec WC596G;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186