



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL5965VY Valise Plug, 15A 125V, 5-15P, YI** *Hubbell Wiring Devices*

Catalog Number	HBL5965VY
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow, Single Pack.
Weight per unit	0.1000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	15
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	15
Material	Polycarbonate
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	1875
Wire Size	#18 AWG to #12 AWG

### **Dimensions and Weight**

Size	1.88 in x 1.88 in x 2.55 in
------	-----------------------------

### **Descriptions**

Description	VALISE PLUG, 15A 125V, 5-15P, YL
extra long description	HWDK HBL5965VY VALISE PLUG, 15A 125
Long Description	Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow, Single Pack.
Product Type	Valise Plug, 15A 125V, 5-15P, YI
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013091
Manufacturers Part Number	HBL5965VY
series	Valise®
UPC	783585013091



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

## Packaging

Carton	10
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Industrial/Commercial Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-15P
standard	CSA Certified to C22.2 No 42 File 280C;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706