



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL8452C Plug, Ang, 3P4W, 50A 3PH 250V, 15-50P, BK *Hubbell Wiring Devices*

Catalog Number	HBL8452C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Plug, Industrial Grade, 3-Pole 4-Wire Grounding, 50A 3 Phase 250V Ac, 15-50P, Black, Single Pack.
Weight per unit	0.8500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	50
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	50
Material	COMPOSITE
Number of Wires	4-Wire
pallet quantity	765
Phase	3
Poles	3-Pole
Voltage Rating	250
Wattage	12500;12500.0000
Wire Size	#12 to #4

Dimensions and Weight

Size	Standard Sized
------	----------------

Descriptions

Description	PLUG,ANG,3P4W, 50A 3PH 250V,15-50P,BK
extra long description	HWDK HBL8452C PLUG,ANG,3P4W, 50A 3P
Long Description	Straight Blade Devices, Plug,Industrial Grade, 3-Pole 4-Wire Grounding, 50A 3 Phase 250V AC, 15-50P, Black, Single Pack.
Product Type	Plug, Ang, 3P4W, 50A 3PH 250V, 15-50P, BK
Special Features	Angled, 4-Position

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015170
Manufacturers Part Number	HBL8452C
series	Extra Heavy Duty
UPC	783585015170

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.85

Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	15-50P
standard	NEMA WD1 and WD5, UL498