



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBLDS3P Disconnect, 30A Unfused, 4X, Led Lights

Hubbell Wiring Devices

Catalog Number	HBLDS3P
Manufacturer	Hubbell Wiring Devices
Description	Disconnect Switches, 30A 600V Ac, 3-Pole, Unfused, Nema 4X Enclosure, Led Illumination
Weight per unit	2.8 (lbs/each)
Product Category	20170811092243

Features

amperage rating	30
connection	Terminal Screws
Material	COMPOSITE
Poles	3
Voltage Rating	480V AC

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	DISCONNECT, 30A UNFUSED, 4X,LED LIGHTS
extra long description	HWDK HBLDS3P DISCONNECT, 30A UNFUSE
Features	Hubbell's new 30A Circuit-Lock Disconnect with integral phase indication LEDs redefines the benchmark for safety by providing insight into the enclosure while in use. Six highly visible LEDs (3 line side/3 load side) display the electrical status of the switch by phase. This voltage detection feature significantly improves existing safety and maintenance procedures by visually providing critical information, such as a welded contact or dropped phase, to personnel prior to removing the enclosure cover. With
Long Description	Disconnect Switches, 30A 600V AC, 3-Pole,Unfused, NEMA 4X Enclosure, LED Illumination
Product Type	Disconnect, 30A Unfused, 4X, Led Lights
Special Features	Switched

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585365107
Manufacturers Part Number	HBLDS3P
series	Non-Fused
UPC	783585365107

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Disconnect Switches



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 2.75

Uses, Certifications, and Standards

Application LED Indicators / Labelless

Enclosure Type 4X, IP69k

environmental conditions NEMA 4X, IP69K

Mounting Mounting Feet

standard UL498 and IEC 60309