

Eaton HFD3040

Catalog Number: HFD3040

Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 40 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HFD3040
	UPC
	786679175842

Product Length/Depth	Product Height
3.38 in	6 in

Product Width	Product Weight
4.13 in	4.3 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

40 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

HFD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50/60 Hz

Interrupt rating

100 kAIC at 240 Vac

65 kAIC at 480 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Multi-wire lugs product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Motor protection circuit breakers product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[HFD3 3D Inventor](#)

[HFD3 2D PDF](#)

[HFD3 2D Drawing Xchange](#)

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[HFD3 3D Model Xchange](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C J-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)

Series C F-Frame molded case circuit breakers

Eaton Specification Sheet - HFD3040



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)