

Eaton HFD2020

Catalog Number: HFD2020

Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 20 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HFD2020
	UPC
	786679175378
Product Length/Depth	Product Height
3.38 in	6 in
Product Width	Product Weight
2.75 in	3.05 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

20 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

HFD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50/60 Hz

Interrupt rating

65 kAIC at 480 Vac

100 kAIC at 240 Vac

Number of poles

Two-pole

Resources

Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Motor protection circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Counterfeit and Gray Market Awareness Guide](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[HFD2 2D Drawing Xchange](#)

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

[HFD2 3D Inventor](#)

[HFD2 2D PDF](#)

[HFD2 3D Model Xchange](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - HFD2020](#)

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)

Series C G-Frame molded case circuit breakers time current curves

MOEM MCCB product selection guide



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)