

Specifications



Eaton HMCPE007C0C

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 7 A, Three-pole, 480 V, Adjustable, Frame J-K, 21-70 A, 600 Y/347 V, Series G, Non-aluminum

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory motor protection
CATALOG NUMBER	HMCPE007C0C
UPC	786679113646
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	CSA Certified UL Listed
GLOBAL CATALOG	HMCPE007C0C
PRODUCT TYPE	Molded case circuit breaker accessory

Product specifications

AMPERAGE RATING	7 A
VOLTAGE RATING	480 V
TRIP TYPE	T98
FRAME SIZE	Frame J-K
MAGNETIC TRIP RANGE	21-70 A
VOLTAGE - MAX	600 Y/347 V
SERIES	Series G
TERMINAL MATERIAL	Non-aluminum
NUMBER OF POLES	Three-pole
TYPE	Motor circuit protector

Resources

APPLICATION NOTES

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Current limiting molded case circuit breaker module product aid](#)

[StrandAble terminals product aid](#)

[Motor protection circuit breakers product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Series G MCCB quick selector](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

BROCHURES

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

[NG and ND-Frame molded
case circuit breakers](#)

[Eaton Specification Sheet -
HMCPE007COC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

