

Specifications



Photo is representative



Eaton HMCPE015E0C

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 15 A, Three-pole, 480 V, Adjustable, Frame J-K, 45-150 A, 600 Y/347 V, Series G, Non-aluminum

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory motor protection
CATALOG NUMBER	HMCPE015E0C
UPC	786679113653
PRODUCT LENGTH/DEPTH	2.99 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed CSA Certified
GLOBAL CATALOG	HMCPE015E0C
PRODUCT TYPE	Molded case circuit breaker accessory

Product specifications

AMPERAGE RATING	15 A
VOLTAGE RATING	480 V
TRIP TYPE	T98
FRAME SIZE	Frame J-K
MAGNETIC TRIP RANGE	45-150 A
VOLTAGE - MAX	600 Y/347 V
SERIES	Series G
TERMINAL MATERIAL	Non-aluminum
NUMBER OF POLES	Three-pole
TYPE	Motor circuit protector

Resources

APPLICATION NOTES

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Multi-wire lugs product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Series G MCCB quick selector](#)

[Circuit breaker motor operators product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - HMCPE015E0C](#)

[NG and ND-Frame molded case circuit breakers](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

