Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HSTT100C 25.4MM 100' Roll BLK Thinwall HS

Panduit Corporation

Catalog Number	HSTT100C
Manufacturer	Panduit Corporation
Description	The HSTT100-C Thin Wall Heat Shrink Tubing Shrinks Around Wires, Connectors, Joints, and Terminals When Heated to Protect Against Abrasion. Applications Include Insulating and Protecting Wires/Cables In Indoor, Dry Locations. Shrink Ratio: 2:1. Temperature Range: -67°F to 275°F (-55°C to 135°C). Flame Retardant, Cross-Linked Polyolefin. 1.00” Diameter X 100’ Long (25.4 MM X 30.5 M). Color Black. 1 Roll.
Weight per unit	4.6 (lbs/each)
Product Category	Insulating Materials

Features

flammability	Flame Retardant
media	Yes
outside diameter	1
Shrink Ratio	2:1

Material, Color, and Finish

Color	Black

Dimensions and Weight

Thickness	0.035

Descriptions

Description	25.4MM 100' ROLL BLK THINWALL HS
extra long description	PAN HSTT100-C Dry-Shrink™ HSTT100-C
Long Description	The HSTT100-C Thin Wall Heat Shrink Tubing shrinks around wires, connectors, joints, and terminals when heated to protect against abrasion. Applications include insulating and protecting wires/cables in indoor, dry locations. Shrink ratio: 2:1. Temperature range: -67°F to 275°F (-55°C to 135°C). Flame retardant, cross-linked polyolefin. 1.00” Diameter x 100’ Long (25.4 mm x 30.5 m). Color Black. 1 roll.
Product Type	Dry-Shrink™ HSTT100-C Heatshrink, Black, Po, 100' L, 1" to 0

Manufacturer Information

Brand	PANDUIT
GTIN	00074983913916
Manufacturers Part Number	HSTT100-C
UPC	074983913916

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type	Heat-Shrink

Packaging

Carton	1
Weight Per roll	4.55

Uses, Certifications, and Standards

Application	For Dry Locations;Insulating and protecting wires and cables
standard	Mil Spec: AMS-DTL-23053/5 Class 1;UL: E122770