



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HSTT50485C HSTT50485C HT Shrink Tubi *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | HSTT50485C |
| Manufacturer | Panduit Corporation |
| Description | Thin Wall Heat Shrink, .50" (12.7MM) Diameter, Clear Cross-Linked Polyolefin, 5 PC. Package Quantity. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Insulating Materials |

Features

| | |
|-------------------------------|------|
| continuous operating temperat | 275 |
| flammability | N/A |
| Inside Diameter | 0.25 |
| media | Yes |
| outside diameter | 0.5 |
| Shrink Ratio | 2:1 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Clear |
|-------|-------|

Dimensions and Weight

| | |
|-----------|-------|
| Thickness | 0.025 |
|-----------|-------|

Descriptions

| | |
|------------------------|---|
| Description | HSTT50485C HT SHRINK TUBI |
| extra long description | PAN HSTT50-48-5C Dry-Shrink™ HSTT50 |
| Long Description | Thin wall heat shrink, .50" (12.7mm) diameter, clear cross-linked polyolefin, 5 pc. package quantity. |
| Product Type | Dry-Shrink™ HSTT50-48-5C Heat Shrink |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983906642 |
| Manufacturers Part Number | HSTT50-48-5C |
| UPC | 074983906642 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | HEAT/COLD SHRINK |
| Type | Heat Shrink Tubing |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|---|
| Carton | 5 |
| Weight Per each | 1 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------------|
| Application | For Dry Locations |
| standard | UL Recognized, CSA Approved, MIL SPEC |