



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



HT8HFRV7 Indicating Light, 120V FV Incand, Red

Eaton Corp

Catalog Number	HT8HFRV7
Manufacturer	Eaton Corp
Description	Eaton HT800 Pushbutton, Watertight and Oiltight-HT800, Indicating Light Unit, Standard Actuator, Chrome, Incandescent, Full Voltage, Nema 3, 3R, 4, 4X, 12 and 13, Illuminated, Red, 120 Vac/DC, Momentary, 30.5 MM
Weight per unit	0.4000 (lbs/each)
Product Category	Pilot Light Complete Assemblie

Features

dimensions	2.4000 IN X 2.1000 IN X 3.2000 IN
media	Yes

Material, Color, and Finish

Style	30.5 mm
-------	---------

Descriptions

Description	INDICATING LIGHT, 120V FV INCAND, RED
extra long description	ETN HT8HFRV7 INDICATING LIGHT, 120V
Features	Eaton's HT800 series features a wide variety of devices, including momentary, illuminated and mushroom head pushbuttons, selector switches, indicating lights and push-pull switches. They are corrosion resistant and water- and oil-tight devices that are suitable for industrial applications, including replacement of other manufacturer's 30.5 mm pushbutton devices.
Long Description	Eaton HT800 pushbutton, Watertight and Oiltight-HT800, Indicating Light Unit, Standard actuator, Chrome, Incandescent, Full voltage, NEMA 3, 3R, 4, 4X, 12 and 13, Illuminated, Red, 120 Vac/dc, Momentary, 30.5 mm
Product Type	Indicating Light, 120V FV Incand, Red

Manufacturer Information

Brand	Eaton
GTIN	00782113565552
Manufacturers Part Number	HT8HFRV7
UPC	782113565552

Taxonomies, Classifications, and Categories

Category Description	PUSHBUTTONS & CHIMES
Type	PUSHBUTTON

Packaging

Carton	1
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

UL Listed, CSA Certified