



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HUB250DN 2-1/2" Rigid Watertite Die Cast Hub

*Appleton/Oz Gedney*

Catalog Number	HUB250DN
Manufacturer	Appleton/Oz Gedney
Description	Watertight Hubs, Zinc Diecast Hubs - Insulated, Class I, Div 2, Trade Size: 2-1/2", Body Length: 1.56", Thread Length: 1.06", Outside Diameter: 3.72"
Weight per unit	1.7 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

Material	Zinc Die Cast
----------	---------------

### Dimensions and Weight

Size	2-1/2
------	-------

### Descriptions

Description	2-1/2" RIGID WATERTITE DIE CAST HUB
extra long description	EGS HUB250DN 2-1/2 ZDC WATER LIGHT
Long Description	Watertight Hubs, Zinc Diecast Hubs - Insulated, Class I, Div 2, Trade Size: 2-1/2", Body Length: 1.56", Thread Length: 1.06", Outside Diameter: 3.72"
Product Type	2-1/2 ZDC Water Light Hubs
Special Features	2-1/2 IN Trade Size Hub, Hole Dia. Min 2.86 IN, Hole Dia. Max 3.00 IN, Panel Thickness Min. 0.06 IN, Panel Thickness Max. 0.31 IN, Insulated Throat

### Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855002177
Manufacturers Part Number	HUB250DN
UPC	687855002177

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Watertight Hubs

### Packaging

Carton	5
Package	25
Weight Per each	1.74



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Used to Connect Rigid or IMC Conduit to a Threadless Opening in an Enclosure
standard	UL Standard: 514B; UL Listed: E14814; CSA Standard: C22.2 No. 18.3; CSA Certified: 065178; NEMA: FB-1
Temperature Rating	105 Degree