



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICN2S110SC (2)F96T12/Ho Bal *Advance By Signify*

Catalog Number	ICN2S110SC
Manufacturer	Advance By Signify
Description	The Right Fit For Your High-Output Applications. Intellivolt Versions Now Available, 1/2-Lamp Operation Of 8' 95/110W T12 Slimline Lamps;Improved Efficiency Over Magnetic Counterparts;Lighter Weight With The Same Mounting and Wiring Configuration No Matter What The Conditions Require, Operating At A Variety Of Line Voltages Between 120V to 480V, Whether Located In High Ambient Temperature Environments (Requiring A 90° C Rating) or Not, Our Family Of Philips Advance Centium Ballasts Are Ideal For A Wide Var
Weight per unit	1.4 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Factor	0.9
Lamp Type	T12
Number of Lamps	2
Power Factor	0.98
start type	Rapid Start
total harmonic distortion	10
Voltage Rating	120-277
Wattage	110
Wire Type	SOLID

Material, Color, and Finish

Housing Material	Metal
------------------	-------

Dimensions and Weight

Height	4.65
Width	0.67



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

extra long description	ADV 199786 ELE BALLAST (2) F96T12/H
Long Description	The right fit for your high-output applications. IntelliVolt versions now available, 1/2-lamp operation of 8' 95/110W T12 slimline lamps;Improved efficiency over magnetic counterparts;Lighter weight with the same mounting and wiring configuration No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide var
Product Type	Ele Ballast (2) F96T12/Ho 120-277V
Special Features	UL, CSA, DOE, CSA-E, RoHS

Manufacturer Information

Brand	Advance
GTIN	00781087085288
Manufacturers Part Number	199786
UPC	781087085288

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Electronic Fluorescent

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	10
Weight Per each	1.38

Uses, Certifications, and Standards

Frequency Rating	50to60
standard	CSA certificate;UL certificate;CEC Listing;Circle E logo;CSA E;DOE;RoHS Compliant