



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ICN3P32N35M 120-277V Elec Bal *Advance By Signify*

Catalog Number	ICN3P32N35M
Manufacturer	Advance By Signify
Description	The Right Choice For A Broad Range Of New Construction and Retrofit Applications Compatible With Energy Saving Lamps;Eligible For Utility Rebates;Maximizes Fixture Design;Reduces Packaging Waste Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology. Intellivolt (120-277V) Input Voltage Range;Lamp Striation Reduction;Meets Nema Premium/Cee;Smallest Enclosure In Industry General Office Lighting, Institutional, Gover
Weight per unit	0.8600 (lbs/each)
Product Category	Electronic Linear Fluorescent

### Features

amperage rating	0.71-0.31
ANSI Code	N/A
Ballast Factor	0.88
dimnable	Non Dimmable
Lamp Type	Fluorescent
Minimum Starting Temperature	-20
Number of Lamps	3
Power Factor	0.98
start type	Instant
total harmonic distortion	<=10
Voltage Rating	120-277
Wattage	87-85

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Height	3.94
Length	3.74
Width	5.12



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	120-277V ELEC BAL
extra long description	ADV 109116 ELE BALLAST (3) F32T8 12
Long Description	The right choice for a broad range of new construction and retrofit applications Compatible with Energy Saving lamps;Eligible for Utility Rebates;Maximizes fixture design;Reduces packaging waste Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology. IntelliVolt (120-277V) input voltage range;Lamp Striation Reduction;Meets NEMA Premium/CEE;Smallest enclosure in industry General office lighting, institutional, gover
Product Type	Ele Ballast (3) F32T8 120-277V
Special Features	IntelliVolt 120-277V, Parallel Lamp Operation

## Manufacturer Information

Brand	Advance
GTIN	00781087091500
Manufacturers Part Number	109116
UPC	781087091500

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	ELECTRONIC

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	0.86

## Uses, Certifications, and Standards

Application	Commercial
Frequency Rating	50to60
Mounting standard	8.9 CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;NOM certificate;RoHS Compliant