ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



IPLD303C 3/0-6AWG 3PRT Insltd Tap Conn

Nsi Industries

Catalog Number	IPLD303C
Manufacturer	Nsi Industries
Description	The Polaris IPLD3/0-3C Multi-Tap Dual-Sided Entry Vision Tap Connector Features 3 Ports Sized For 3/0 - 6 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications
Weight per unit	0.3100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	3
Poles	1
Voltage Rating	600
Warranty	1 YEAR
Wire Size	3/0-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Clear
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=2.630 - W=1.830 - H=1.790

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Descriptions

Description	3/0-6AWG 3PRT INSLTD TAP CONN
extra long description	NSI IPLD3/0-3C Polaris Vision Tap (
Features	The Polaris IPLD3/0-3C 3-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 3/0 - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal co
Long Description	The Polaris IPLD3/0-3C Multi-Tap Dual-Sided Entry Vision Tap Connector features 3 ports sized for 3/0 - 6 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications
Product Type	Polaris Vision Tap (Clear) 3/0-6 Awg Polaris Insulated Mult
Special Features	(3) 3/0-6 AWG - Dual Rated

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381996480
Manufacturers Part Number	IPLD3/0-3C
UPC	662381996480

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Double Sided Entry

Packaging

Carton	6
Weight Per each	0.31

Uses, Certifications, and Standards

Application	Wire Termination
Enclosure	Clear Plastisol
environmental conditions	Dry Location Only
standard	UL 486A/B
Temperature Rating	90