



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPLD50012 500MCM 12port

Nsi Industries

| | |
|------------------|---|
| Catalog Number | IPLD50012 |
| Manufacturer | Nsi Industries |
| Description | The Polaris IPLD500-12 Multi-Tap Dual-Sided Entry Connector Features 12 Ports Sized For 500 MCM - 4 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Tra |
| Weight per unit | 3.1 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|---------------|
| Material | Aluminum |
| Number of Conductors | 12 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 500 MCM-4 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Black |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|------------------------------|
| Size | L=14.400 - W=2.830 - H=2.910 |
|------|------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 500MCM 12PORT |
| extra long description | NSI IPLD500-12 POLARIS Ins Multi-Ta |
| Features | The Polaris IPLD500-12 12-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to twelve conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 500 MCM - 4 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric |
| Long Description | The Polaris IPLD500-12 Multi-Tap Dual-Sided Entry Connector features 12 ports sized for 500 MCM - 4 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable tra |
| Product Type | Polaris Ins Multi-Tap 500 12 Port Dse |
| Special Features | (12) 500 MCM-4 AWG - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381925107 |
| Manufacturers Part Number | IPLD500-12 |
| UPC | 662381925107 |

Taxonomies, Classifications, and Categories

| | |
|------|--------------------|
| Type | Double Sided Entry |
|------|--------------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 3.13 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL 486A/B |
| Temperature Rating | 90 C |