



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPLG303 Insd Multi-Tap Conn

*Nsi Industries*

Catalog Number	IPLG303
Manufacturer	Nsi Industries
Description	Multi-Port Connector, #4 Awg Conductor Size, 3/0 Awg Conductor Size, Insulated, Plastisol Insulation Material, Copper Conductor Material, Gray Insulation Color, 3 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 2.25 In Overall Length, 600 V Ac, 0.28 LB/Ea
Weight per unit	0.2800 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	3
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	(Class B,C,D) 3/0-4 AWG - (Class K,M,I) 2/0-2 AWG
Wire Type	B,C,D,K,M,I

### Material, Color, and Finish

Color	Grey
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=2.250 - W=1.600 - H=1.750
------	-----------------------------

### Descriptions

Description	INSD MULTI-TAP CONN
extra long description	NSI IPLG3/0-3 POLARIS Grey Multi-Ta
Features	The Polaris IPLG3/0-3 3-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to three fine-stranded wire conductors in applications including cable trays, troughs, wire-ways, raceways, ducts and motor junction boxes. Sized for 3/0 - 4 AWG wires and rated for 600V, this connector installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength plastisol insulat

### Manufacturer Information

GTIN	00662381951557
UPC	662381951557



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... T&B C TAP LUGS

Type ..... Single Sided Entry

## Packaging

Carton ..... 6

Weight Per each ..... 0.28

## Uses, Certifications, and Standards

Application ..... Wire Termination

environmental conditions ..... 90 C

standard ..... UL 486A/B

Temperature Rating ..... 90 C