

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street 74701-0000, OK Durant Phone: 580-745-5448 Fax: 580-745-5449



IPLG304 IPLG3/0-4 Fine STR Wire

Nsi Industries

Catalog Number	IPLG304
Manufacturer	Nsi Industries
Description	The Polaris IPLG3/0-4 Grey Multi-Tap Single Side Entry Connector Features 4 Ports Sized For 3/0 - 4 Awg Class B, C or D Wires or 2/0 - 2 Awg Class K, M or I Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Specially Designed For Fine-Stranded Copper Wires With A Pre-Installed Tin Plated Copper Ferule That Collapses As The Screw Is Tightened to Form A Strong Connection With Fine-Stranded Wires. Removable Access Plugs Cover The Hex Screws Used to Tighten TH
Weight per unit	
Product Category	Large Terminals & Connectors
Features	
Number of Conductors	4
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	(Class B C D) 2/0 4 ANNC (Class K A I) 2/0 2 ANNC
Wire Type	B,C,D,K,M,I
Material, Color, and Finish	
Color	Gray
Finish	Plastisol Insulated
Housing Material	Aluminum
Dimensions and Weight	
Size	L=2.900 - W=1.600 - H=1.750



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street 74701-0000, OK Durant Phone: 580-745-5448 Fax: 580-745-5449

Descriptions	
Description	IPLG3/0-4 FINE STR WIRE
extra long description	NSI IPLG3/0-4 POLARIS Grey Multi-Ta
Features	The Polaris IPLG3/0-4 4-Port Single-Side Connector provides the
	simplest solution for forming a secure connection between up to
	four fine-stranded wire conductors in applications including cable
	trays, troughs, wire-ways, raceways, ducts and motor junction
	boxes. Sized for 3/0 - 4 AWG wires and rated for 600V, this
	connector installs faster than traditional uninsulated connector
	options using just a hex key and torque wrench. The aluminum
D 11	alloy body is wrapped in high-dielectric strength plastisol insulati
Long Description	The Polaris IPLG3/0-4 Grey Multi-Tap Single Side Entry Connector
	features 4 ports sized for 3/0 - 4 AWG Class B, C or D wires or 2/0 - 2 AWG Class K, M or I wires. The body is made from aluminum
	alloy wrapped in a layer of plastisol insulation. Each port is
	specially designed for fine-stranded copper wires with a
	pre-installed tin plated copper ferule that collapses as the screw
	is tightened to form a strong connection with fine-stranded
	wires. Removable access plugs cover the hex screws used to
	tighten th
Product Type	Polaris Grey Multi-Tap 3/0 4 Port
Special Features	(4) 3/0-4 AWG Class B,C,D - (4) 2/0-2 AWG Class K,M,I
Manufacturer Information	
Brand	Polaris
GTIN	00662381951564
Manufacturers Part Number	IPLG3/0-4
UPC	662381951564
Taxonomies, Classifications, and Cate	egories
Category Description	Comp & Mech Lugs and Butt Splices
Туре	Single Sided Entry
Packaging	
Carton	6
Weight Per each	0.37
Uses, Certifications, and Standards	
Application	Wire Termination
environmental conditions	90 C

UL 486A/B