



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ITG30 3/0-#4 Polaris Insul-Tap Connector For Dlo Cable

*Nsi Industries*

Catalog Number	ITG30
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #4 Awg Conductor Size, 3/0 Awg Conductor Size, Insulated, Plastisol Insulation Material, Copper Conductor Material, Gray Insulation Color, 2 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 1.85 In Overall Length, 600 V Ac, 0.19 LB/Ea
Weight per unit	0.1900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	(Class B,C,D) 3/0-4 AWG - (Class K,M,I) 2/0-2 AWG
Wire Type	B,C,D,K,M,I

### Material, Color, and Finish

Color	Grey
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=1.850 - W=1.600 - H=1.810
------	-----------------------------

### Descriptions

Description	3/0-#4 POLARIS INSUL-TAP CONNECTOR FOR DLO CABLE
extra long description	NSI ITG-3/0 POLARIS Grey Multi-Tap
Features	The Polaris ITG-3/0 2-Port Single-Side Connector provides the simplest solution for forming a secure connection between two fine-stranded wire conductors in applications including cable trays, troughs, wire-ways, raceways, ducts and motor junction boxes. Sized for 3/0 - 4 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrap

### Manufacturer Information

GTIN	00662381951533
UPC	662381951533



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Multi Cable

## Packaging

Carton	6
Weight Per each	0.19

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C