



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JJS40 Tron Fast Acting Fuse Class T

Bussmann Fuses

Catalog Number	JJS40
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series JJS Fuse, Current-Limiting, Small Footprint, VFD Line Protection, 40 A, Class T, Non-Indicating, Ferrule End X Ferrule End, 200 Kaic At 600 V, Standard, 10, 600 V
Weight per unit	0.5000 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

amperage rating	40 A
class	Class T
connection	Ferrule End X Ferrule End
dimensions	1.5600 IN X 0.8100 IN X 0.8100 IN
interrupt rating	200 kAIC at 600 Vac
media	Yes
Voltage Rating	600 V

Dimensions and Weight

Size	1.00 In Diameter X 1.56 In Length
------	-----------------------------------

Descriptions

Description	TRON FAST ACTING FUSE CLASS T
extra long description	BUSS JJS-40 TRON FAST ACTING FUSE C
Features	Bussmann's Class T current-limiting, fast-acting fuses. Provides 10X better current limitation to help prevent equipment damage caused by short-circuit events. 200 kA Interrupting rating complies with NEC Section 110.9 for today's large capacity systems. Small, space-saving fuses provide a high degree of current limitation on short-circuits for excellent component protection.
Long Description	Eaton Bussmann series JJS fuse, Current-limiting, Small footprint, VFD line protection, 40 A, Class T, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 V, Standard, 10, 600 V
Product Type	Tron Fast Acting Fuse Class T
Special Features	Non-Indicating

Manufacturer Information

Brand	Eaton
GTIN	00051712628402
Manufacturers Part Number	JJS-40
UPC	051712628402



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	1
Package	10
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked