

Eaton JP60030-3CR

Catalog Number: JP60030-3CR

Eaton Bussmann series JP pyramid fuse block, CR, 30 A, Class J, 200 kAIC, Thermoplastic, Panel, 600 V, #14-2 AWG Cu/Al

General specifications



Product Name Catalog Number

Eaton Bussmann series JP pyramid fuse block JP60030-3CR

UPC

051712434164

Product Length/Depth

0.001 in

Product Height

0.001 in

Product Width

0.001 in

Product Weight

0.7 lb

Warranty

Not Applicable

Compliances

RoHS Compliant

Certifications

Contact Manufacturer

UL Listed

CSA Certified



Powering Business Worldwide

Electrical rating

Amperage Rating

30 A

Interrupt rating

200 kAIC

Short-circuit rating

200 kA

Voltage rating

600 V

Physical details

Material

Thermoplastic

Wire size

#14-2 AWG Cu/Al

General information

Class

Class J

Mounting method

Panel

Special features

CR

Resources

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Bussmann series full line catalog 1007, section 8 fuse blocks and holders

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

[Eaton Specification Sheet - JP60030-3CR](#)

Technical data sheets

[JP60030-3CR-J PYRAMID FUSE BLOCK](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton JP60030-3CR

Catalog Number: JP60030-3CR

Eaton Bussmann series JP pyramid fuse block, CR, 30 A, Class J, 200 kAIC, Thermoplastic, Panel, 600 V, #14-2 AWG Cu/Al

General specifications



Product Name	Catalog Number
--------------	----------------

Eaton Bussmann series JP pyramid fuse block	JP60030-3CR
---	-------------

UPC

051712434164

Product Length/Depth	Product Height
----------------------	----------------

0.001 in

0.001 in

Product Width	Product Weight
---------------	----------------

0.001 in

0.7 lb

Warranty	Compliances
----------	-------------

Not Applicable

RoHS Compliant

Certifications

Contact Manufacturer

UL Listed

CSA Certified



Powering Business Worldwide

Electrical rating

Amperage Rating

30 A

Interrupt rating

200 kAIC

Short-circuit rating

200 kA

Voltage rating

600 V

Physical details

Material

Thermoplastic

Wire size

#14-2 AWG Cu/Al

General information

Class

Class J

Mounting method

Panel

Special features

CR

Resources

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[Bussmann series full line catalog 1007, section 8 fuse blocks and holders](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - JP60030-3CR](#)

Technical data sheets

[JP60030-3CR-J PYRAMID FUSE BLOCK](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia