



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

K2A31U  
 7818106001533  
 TWO:4STR-350 DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 1.94  
 Length (in) 2.88  
 Bolt Hole Size (in) 0.50  
 Thickness 0.25  
 D - in 1.69  
 Pad Width (in) 1.94  
 N (in) 0.88

**General**

Number of Holes 1  
 Product Description Aluminum Universal Terminal, 2 Conductor, 1 Hole, 6 AWG (Str)-350 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range) 6 STR- 350 kcmil  
 Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 6 AWG-350 kcmil

**Physical**

Installation Torque 275  
 Type of Plating Tin  
 Connector Type Terminal  
 Bolt Hole Size 1/2  
 Plated (Yes or No) N  
 Product Material Aluminum

**Approvals / Certifications**

Rated for Direct Burial N  
 UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Non-Compliant  
 Industry Standards UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

K2A31U  
 7818106001533  
 TWO:4STR-350 DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 1.94  
 Length (in) 2.88  
 Bolt Hole Size (in) 0.50  
 Thickness 0.25  
 D - in 1.69  
 Pad Width (in) 1.94  
 N (in) 0.88

**General**

Number of Holes 1  
 Product Description Aluminum Universal Terminal, 2 Conductor, 1 Hole, 6 AWG (Str)-350 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range) 6 STR- 350 kcmil  
 Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 6 AWG-350 kcmil

**Physical**

Installation Torque 275  
 Type of Plating Tin  
 Connector Type Terminal  
 Bolt Hole Size 1/2  
 Plated (Yes or No) N  
 Product Material Aluminum

**Approvals / Certifications**

Rated for Direct Burial N  
 UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Non-Compliant  
 Industry Standards UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175