



## KS15, Split Bolt Connector, Run/Tap: #10-8 AWG Str

By Burndy  
Catalog # [KS15](#)



Copper Split Bolt, Cu: 10-8 AWG (Str) (Run & Tap).

### Application

For Direct Burial Applications In Earth Or Concrete, Copper

### General

Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	80 in-lbs
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011256
UPC 12 Digit	7818100112566

### Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	0.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

### Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	14 AWG-8 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor - CopperWeld Solid Tap	#8
Conductor - CopperWeld Solid Tap Range	#8
Conductor - CopperWeld Str Run	#8
Conductor - CopperWeld Str Run Range	#8
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Run</li><li>• CU C Str-Run</li><li>• CU Weld C Solid-Run</li><li>• CU Weld C Str-Run</li><li>• CU C Str-Tap</li><li>• CU Weld C Solid-Tap</li><li>• CU Weld C Str-Tap</li><li>• CU C Solid-Tap</li></ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL486</li><li>• UL467</li><li>• CSA C22.2 No 41</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL486</li><li>• UL467</li></ul>

Standards - RoHS Compliance CM  
Status

UL Listed Yes

### Logistics

Carton Quantity 100

Minimum Pack Quantity 1

Pallet Quantity 99000

### Product Assets

[3D Models - KS15\\_MODEL-IGES](#)

[3D Models - KS15\\_MODEL-STEP](#)

[3D Models - KS15\\_MODEL-PDF](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - SD..078561-01](#)



A proud member of the Hubbell Family.