



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTEMRGLED121200K 12W Led Emergency Backup Kit W/1200LM Led Module *Keystone Technologies*

Catalog Number	KTEMRGLED121200K
Manufacturer	Keystone Technologies
Description	Led Emergency Back-Up Kit, 12W Constant Wattage Driver & .70" X 8" Led Module, Approx 1200 Lumens. 90 Minute Operation, 120-277V Input, Remote Battery Pack. Includes Instruction Sheets, Test Switch, and Wiring Accessories. Individually Packaged
Weight per unit	2.5 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1200
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	N/A
color temperature	N/A
housing color	N/A



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	N/A
Description	12W LED EMERGENCY BACKUP KIT W/1200LM LED MODULE
extra long description	Key KT-EMRG-LED-12-1200-K1-IP 28W,
Long Description	LED Emergency Back-Up Kit, 12W Constant Wattage Driver & .70" x 8" LED Module, Approx 1200 Lumens. 90 Minute Operation, 120-277V Input, Remote Battery Pack. Includes Instruction Sheets, Test Switch, and Wiring Accessories. Individually Packaged
Product Type	28W, 7" Round Ac Led Light Engine Kit, Phase Dimming, 90 Cri

Manufacturer Information

Brand	Keystone
GTIN	00890949011652
Manufacturers Part Number	KT-EMRG-LED-12-1200-K1-IP
UPC	890949011652

Taxonomies, Classifications, and Categories

Category Description	PHOTO & PROJECTION
----------------------	--------------------

Packaging

Carton	1
Weight Per each	2.49

Uses, Certifications, and Standards

Energy Star	Y
-------------	---