



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLED15T848GC840 15W Led T8 48" 40K Line Voltage

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | KTLED15T848GC840 |
| Manufacturer | Keystone Technologies |
| Description | 15W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 4, 4000K, Direct Drive |
| Weight per unit | 0.0262 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 2000 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 15 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Shatterproof Glass |
| Description | 15W LED T8 48" 40K LINE VOLTAGE |
| extra long description | Key KT-LED15T8-48GC-840-D /G3-CP 15 |
| Long Description | 15W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 4, 4000K, DIRECT DRIVE |
| Product Type | 15W, 2000 Lumen, 4', 240' Beam Angle, Ballast Bypass, DLC 4. |

Manufacturer Information

| | |
|---------------------------|------------------------------|
| Brand | Keystone |
| GTIN | 00890949013328 |
| Manufacturers Part Number | KT-LED15T8-48GC-840-D /G3-CP |
| UPC | 890949013328 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.0262 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|