

ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



KTK30 30A 600V Fa Midget Fuse Bussmann Fuses

Catalog Number	KTK30
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series KTK Fuse, Control Circuits, Lighting Circuit Protection, Meter Circuits, 30 A, Non-Indicating, Ferrule End X Ferrule End, 100 Kaic At 600 V, Nickel-Plated Bronze Endcap, Melamine Tube, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	30 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
interrupt rating	100000 Amp (RMS Symmetrical UL)
Material	Melamine Tube;Nickel-plated bronze endcap
media	Yes
Voltage Rating	600 VAC

Dimensions and Weight

Size 13/32 In Diameter X 1-1/2 In Length

Descriptions

Description	30A 600V FA MIDGET FUSE
extra long description	BUSS KTK-30 LIMITRON FAST ACTING FU
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series KTK fuse, Control circuits, Lighting circuit protection, Meter circuits, 30 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, Nickel-plated bronze endcap, Melamine tube, 600 V
Product Type	Limitron Fast Acting Fuse
Special Features	Nickel Plated Bronze Endcap

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712420303
Manufacturers Part Number	KTK-30
UPC	051712420303



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Taxonomies, Classifications, and Cate	egories
Category Description	MIDGET FUSES
Туре	FUSE
Packaging	
Carton	10
Weight Per each	0.02
Uses, Certifications, and Standards Application	Ind Facilities & Factories - Facility: Safety and Security Systems

CE Marked, RoHS Compliant