



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLED13A190830 13W Led A19 30K Dim 1600LM 80cri

Keystone Technologies

| | |
|------------------|--|
| Catalog Number | KTLED13A190830 |
| Manufacturer | Keystone Technologies |
| Description | A19 Omni-Directional Bulb, 100W Equivalent, E26 Medium Base, 3000K, 80 Cri |
| Weight per unit | 0.2860 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|---------|
| Ballast Type | N/A |
| beam angle | 230 Deg |
| Circuit Type | N/A |
| Input Voltage | 120V |
| ip rating | N/A |
| lumens | 1600 |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Warranty | 3 |
| Wattage | 13 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | E26 |
| color rendering index (cri) | >80 Deg |
| color temperature | 3000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|--|
| Construction | N/A |
| Description | 13W LED A19 30K DIM 1600LM 80CRI |
| extra long description | Key KT-LED13A19-O-830 100W Equiv., |
| Long Description | A19 Omni-Directional Bulb, 100W Equivalent, E26 Medium Base, 3000K, 80 CRI |
| Product Type | 100W Equiv., 16W, 1600 Lumen, A21, E26, =80 Cri, Dimmable 27 |

Manufacturer Information

| | |
|---------------------------|-------------------|
| Brand | Keystone |
| GTIN | 00843654130255 |
| Manufacturers Part Number | KT-LED13A19-O-830 |
| UPC | 843654130255 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Packaging

Carton 1

Package 60

Weight Per each 0.286

Uses, Certifications, and Standards

Energy Star Y