



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948



L1038 1/0 1-Hole Long Barrel Compression Lug 3/8" Bolt

Nsi Industries

Catalog Number	L1038
Manufacturer	Nsi Industries
Description	1 Hole Long Barrel Copper Compression Lug 1/0 Awg - 3/8" Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Low Contact Resistance. Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed and to Cable Manufacturer Instructions. Temperature Rating 90 Degrees C. .
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	1/0 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Pink
Finish	Tin Plated

Dimensions and Weight

Size	L=2.50 - W=.744 - OD=.520 - ID=.390
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Descriptions

Description	1/0 1-HOLE LONG BARREL COMPRESSION LUG 3/8" BOLT
extra long description	NSI L1038 CMP Lug Cu Long 1/0 AWG 3
Features	1 Hole Long Barrel Copper Compression Lug 1/0 AWG - 3/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded - Pink - for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Long Description	1 Hole Long Barrel Copper Compression Lug 1/0 AWG - 3/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Product Type	CMP Lug Cu Long 1/0 Awg 3/8 Bolt Size
Special Features	1/0 AWG (STR) - 3/8 Mounting Hole

Manufacturer Information

Brand	Polaris
GTIN	00662381034069
Manufacturers Part Number	L1038
UPC	662381034069

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - One Hole

Packaging

Carton	1
Package	50
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)